


## Type 5HT / 5HTP

5 x 20mm Ceramic Tube  
RoHS Compliant

### Time-lag Fuse Series (High - Breaking Capacity)

5HTD1105



#### Electrical Characteristics (IEC-127-2 STANDARD SHEET 5)

Rated Current	1.5 In		2.1 In		2.75 In		4 In		10 In	
	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX
100mA to 3.15A	1	30	1	80	95	5	10	100		
4A and above	1	30	1	80	150	5	20	100		
	hr.	min.	sec	sec	ms	sec	ms	ms		

Approvals

Safety Agency Approvals	Amp range / Volt @ I.R. ability
Certificate No. 408893	1A - 6.3A / 250V AC @ 1,500A
Licence No. 40000505	
Certificate No. EM232	
Recognized File No. E20624 Acceptance File No. LR39772	250mA - 10A / 250V AC @ 1,500A
File No. JET1037-31003-1004, JET1037-31003-1005	1A - 5A / 250V AC @ 1,500A
Licence No. 2002010207021531	250mA - 10A / 250V AC @ 1,500A

#### RoHS Compliant Product

For RoHS Compliant Version, add suffix "R" after catalog number

#### Operating Temperature

-55°C to +125°C

#### Physical Specification

##### Materials

Ceramic body / Nickel Plated Brass Caps

Lead wire:

Tin plated copper alloy,

Diameter 0.032", 6.3A and less

Diameter 0.040", 8A and above

##### Marking

On fuse:

"bel", "T", "Current Rating", "H", "250V",

"Appropriate Safety Logos", "✓" (RoHS Version)

On label:

"bel", "5HT", or "5HTP", "Current Rating",

"Voltage Rating", "Interrupting Rating", "Appropriate Safety Logos" and + suffix "R" for RoHS Version

Catalog Number	RoHS Suffix	Ampere Rating	Typical Cold Resistance (ohm)	Volt-drop @100% In (Volt) max.	Melting I <sup>2</sup> T < 10 mSec (A <sup>2</sup> Sec)	Melting I <sup>2</sup> T @10 In (A <sup>2</sup> Sec)	Maximum Power Dissipation (W)
5HT (P) 100	-R	100mA	18.00	2.05	0.059	0.06	0.27
5HT (P) 160	-R	160mA	12.10	1.80	0.035	0.04	0.28
5HT (P) 200	-R	200mA	8.00	1.50	0.062	0.08	0.30
5HT (P) 250	-R	250mA	3.40	1.20	0.098	0.12	0.34
5HT (P) 315	-R	315mA	2.20	1.00	0.18	0.22	0.38
5HT (P) 400	-R	400mA	1.40	0.75	0.28	0.34	0.41
5HT (P) 500	-R	500mA	1.00	0.70	0.46	0.58	0.48
5HT (P) 630	-R	630mA	0.60	0.52	0.70	0.90	0.55
5HT (P) 800	-R	800mA	0.40	0.45	1.08	1.50	0.64
5HT (P) 1	-R	1A	0.20	0.25	1.70	1.70	0.73
5HT (P) 1.25	-R	1.25A	0.14	0.22	3.00	3.20	0.81
5HT (P) 1.6	-R	1.6A	0.10	0.20	5.40	5.90	0.91
5HT (P) 2	-R	2A	0.07	0.19	9.70	11	1.00
5HT (P) 2.5	-R	2.5A	0.05	0.17	17	20	1.10
5HT (P) 3.15	-R	3.15A	0.04	0.14	31	38	1.20
5HT (P) 4	-R	4A	0.03	0.10	56	69	1.40
5HT (P) 5	-R	5A	0.02	0.11	101	128	1.50
5HT (P) 6.3	-R	6.3A	0.01	0.074	181	237	1.70
5HT (P) 8	-R	8A	0.009	0.092	330	439	2.70
5HT (P) 10	-R	10A	0.007	0.078	601	812	2.90

Consult manufacturer for other ratings

#### Packaging

1. In bulk:

5HT - 1,000 pcs per box; 5HTP - 500 pcs per box


2. On Axial Tape & Reel:

1,500 pcs per reel

3. Tape & Reel specification:

per EIA-296-E & IEC 286-1 @ 10mm Pitch and 63.5mm inside Tape Spacing

#### Mechanical Dimensions



Specifications subject to change without notice


ORDERING INFORMATION SEE LAST 2 PAGES

**Type 5HT / 5HTP**  
**Time-lag Fuse Series (High - Breaking Capacity)**

5 x 20mm Ceramic Tube  
 RoHS Compliant

5HTC0405

**5HT / 5HTP - TIME CURRENT CHARACTERISTIC CURVE**



Specifications subject to change without notice

NOTE - see important information under "User Guide" on P.08

**Corporate Office**  
**Bel Fuse Inc.**  
 206 Van Vorst Street, Jersey City, NJ 07302  
 Tel: 201-432-0463  
 Fax: 201-432-9542  
 E-Mail: [belfuse@belfuse.com](mailto:belfuse@belfuse.com)  
 Website: [www.belfuse.com](http://www.belfuse.com)

**Far East Office**  
**Bel Fuse Ltd.**  
 8F/8 Luk Hop Street  
 San Po Kong  
 Kowloon, Hong Kong  
 Tel: 852-2328-5515  
 Fax: 852-2352-3706

**European Office**  
**Bel Fuse Europe Ltd.**  
 Preston Technology Management Centre  
 Marsh Lane, Preston PR1 8UD  
 Lancashire, U.K  
 Tel: 44-1772-556601  
 Fax: 44-1772-888366