



Detector/Amplifier Hybrids Without Feedback Resistor BLUE ENHANCED SD 444-42-22-261





FEATURES

- Low noise
- Blue enhanced
- Custom feedback
- High speed

DESCRIPTION

The **SD 444-42-22-261** is a detector/amplifier hybrid that combines a silicon photodiode with an opamp without the feedback resistor and capacitor, available

in a hermetic metal can package.


APPLICATIONS

- Instrumentation
- Industrial
- Medical

SYMBOL TYP PARAMETER MIN MAX UNITS ± 18 V_{s} Voltage Supplies ± 5 ± 15 V Vio Input Offset Voltage 1 2 mV Input Voltage Noise Vn nV/√Hz 12 @ f = 10KHz Input Bias Current 15 40 pА l_{ib} Input Offset Current 20 30 pА I_{io} Input Current Noise fA/√Hz 20 30 I_n @ f = 10KHz I_{S} Supply Current 6.5 7 mΑ GBP Gain Bandwidth Product 18 MHz Storage Temperature -65 +125 °C $\mathsf{T}_{\mathsf{STG}}$ °C **Operating Temperature** -40 +85 To

AMPLIFIER SPECIFICATIONS (TA)= 23°C UNLESS OTHERWISE NOTED

SPECTRAL RESPONSE




DETECTOR SPECIFICATIONS (TA)= 23°C UNLESS OTHERWISE NOTED

SYMBOL	CHARACTERISTIC	TEST CONDITIONS	MIN	TYP	MAX	UNITS
I _D	Dark Current	V _R = 10 V			150	nA
R _{SH}	Shunt Resistance	V _R = 0 V	15			ΜΩ
CJ	Junction Capacitance	$V_R = 0 V$, $f = 1 MHz$		1700		рF
		$V_{R} = 10 V, f = 1 MHz$		340		
λ range	Spectral Application Range	Spot Scan	250		1100	nm
R	Responsivity	λ = 450 nm, V _R = 0 V		0.28		



SCHEMATIC AND CONNECTION DIAGRAM



Information in this technical datasheet is believed to be correct and reliable. However, no responsibility is assumed for possible inaccuracies or omission. Specifications are subject to change without notice.

Advanced Photonix Inc. 1240 Avenida Acaso, Camarillo CA 93012 • Phone (805) 987-0146 • Fax (805) 484-9935 • www.advancedphotonix.com